

## LED pen torch with batteries, Type: PEN



### **Order data**

Order number	081461 PEN
GTIN	4062406056889
Item class	02A

### **Description**

#### **Version:**

Handy LED pen torch with **focussable lamp head** for bundled and concentrated illumination between 10° and 80°. Practical pocket clip and push-button.

#### **Function:**

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

IP Index of Protection: IP 54 Torch function: Focus

ATEX zone: no Illumination: 120 lm Working life: 6 h

Number of batteries contained: 2

Battery type: Micro, AAA Overall length: 130 mm

## **Technical description**

Micro, AAA



IP Index of Protection	IP 54
Working life	6 h
ATEX zone	no
Weight	60 g
Bulb	LED module
Head ∅	17 mm
Illumination	120 lm
Number of batteries contained	2
Torch function	Focus
Overall length	130 mm
Power supply	Battery-powered
Type of product	Flashlight

# **Accessories**

Alkaline-manganese batteries International size LR3	081552 LR3
Alkaline-manganese batteries International size LR3	081553 LR3
Alkaline-manganese batteries International size LR3	081554 LR3
Alkaline manganese battery set International size LR3	081558 LR3
Lithium-metal batteries International size LR3	081559 LR3
Alkaline-manganese batteries International size LR3	081561 LR3
Alkaline manganese battery set International size LR3	081557 LR3
Alkaline-manganese batteries International size LR3	081551 LR3