

## LED torch, black with batteries, Type: 160



## **Order data**

Order number	081533 160
GTIN	4062406087173
Item class	02A

### **Description**

#### **Version:**

High-quality, long-life and sturdy LED torch of anodised aluminium. **Latest LED technology** with **outstanding lighting power**.

- · Anti-roll protection.
- · Rubber cover for the operating button.

With **focussable** lamp head.

#### **Function:**

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

IP Index of Protection: IP 54

Torch function: Focus

ATEX zone: no Illumination: 250 lm Working life: 9 h

Number of batteries contained: 2

Battery type: Mignon, AA Overall length: 160 mm

# **Technical description**

# Data sheet

Battery type	Mignon, AA
Working life	9 h
Number of batteries contained	2
ATEX zone	no
IP Index of Protection	IP 54
Illumination	250 lm
Torch function	Focus
Overall length	160 mm
Power supply	Battery-powered
Type of product	Flashlight

# **Accessories**

Alkaline-manganese batteries International size LR6	081552 LR6
Lithium-metal batteries International size LR6	081559 LR6
Alkaline-manganese batteries International size LR6	081551 LR6
Alkaline manganese battery set International size LR6	081557 LR6
Alkaline manganese battery set International size LR6	081558 LR6
Alkaline-manganese batteries International size LR6	081561 LR6
Alkaline-manganese batteries International size LR6	081556 LR6
Alkaline-manganese batteries International size LR6	081553 LR6
Alkaline-manganese batteries International size LR6	081554 LR6