

LED rechargeable pen light, Type: 170



Order data

Order number	081579 170
GTIN	4062406056872
Item class	02A

Description

Version:

LED rechargeable pen light with main beam and spotlight, with a pocket clip with powerful attachment magnet. Magnetic base with 360° rotation.

Function:

IP20: Protected against penetration by foreign bodies with $\emptyset < 12$ mm, however touching should be avoided, and offers no protection against water.

Supplied with:

Including USB charging cable. IP Index of Protection: IP 20 ATEX zone: no Illumination: 220 Im Illumination step 2: 80 Im Working life: 2.5 h Number of rechargeable batteries contained: 1 Type of rechargeable battery: Lithium-ion

Technical description

Illumination

220 lm

© Hoffmann GmbH Qualitätswerkzeuge

Data sheet

Working life	2.5 h
Battery voltage	3.7 V
ATEX zone	no
Weight	83 g
Battery capacity	1.1 A·h
Bulb	LED module
Illumination step 2	80 lm
IP Index of Protection	IP 20
Number of rechargeable batteries contained	1
Overall length	170 mm
Type of rechargeable battery	Lithium-ion
Overall width	20 mm
Power supply	Rechargeable battery-powered
Type of product	Flashlight