HOLEX

Digital caliper ABS with data output, Measuring range: 150mm



Order data

Order number	412805 150
GTIN	4045197574404
Item class	42A

Description

Version:

Large, sharp-contrast digital display. The measuring faces are precision-lapped. Digital caliper with **absolute scale**, no zeroing required. Electronics switch off automatically after approx. 5 minutes and switch on again as soon as the tool is moved.

- $\cdot\,$ Very high accuracy due to the glass scale.
- The electronics are decoupled from the casing and incorporated directly in the sliding part. The gauging force is transmitted directly to the measurement jaws. This reduces the liability of the caliper to errors and increases the working life.

· With sturdy metal body.

Supplied with:

Battery No. 081560 size CR1632.

Optional extras:

Keyboard interface No. 498969 size USB. Packaging: sturdy box Standard: ISO 13385 Reversible reading: mm / inch Depth gauge: rectangular 3.7×1.3 Measured value saving: Once-off setting of the zero position Calibration: A1 Scale divisions: 0.01 mm Scale divisions: 0.0005 in Jaw length: 40 mm

Technical description

roup 🔥

Data sheet

Depth gauge available	yes
Jaw length	40 mm
Standard	ISO 13385
Depth gauge	rectangular 3.7×1.3
Calibration	A1
Auto switch-off	yes
Reversible reading	mm / inch
Scale divisions	0.01 mm
Scale divisions	0.0005 in
Measuring range	0 - 150 mm
Measured value saving	Once-off setting of the zero position
Article no of the battery / rechargeable battery fitted	081560 CR1632
Number of batteries contained	1
Power supply	Battery-powered
Measurement deviation E MPE	±0.03 mm
Interface	USB interface
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

Calibration Calipers / depth gauges maximum measuring range 200 mm	011030 200
Labelling laser-etched Type	018940
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	011050 200
Calibration Calipers / depth gauges maximum measuring range 200 mm	021000 200

DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	021010 200
Accessories	
Plastic case Type MS150	412468 MS150
Keyboard interface USB Type USB	498969 USB
Plastic case Type MS150	412470 MS150
Screw for depth gauge holder	412230
Button cell / special battery Battery type CR1632	081560 CR1632