



Digital caliper ABS, Measuring range: 100mm



Order data

Order number	412821 100
GTIN	4045197771780
Item class	42A

Description

Version:

Large high-contrast digital display. The measuring faces are precision-lapped. Incremental measuring system without absolute scale.

Supplied with:

Battery No. 081560 size LR44.
 Packaging: sturdy box
 Standard: ISO 13385
 Reversible reading: mm / inch
 Depth gauge: rectangular 3.7×1.3
 Calibration: A1
 Scale divisions: 0.01 mm
 Scale divisions: 0.0005 in
 Jaw length: 30 mm

Technical description

Calibration	A1
Scale divisions	0.01 mm
Scale divisions	0.0005 in
Depth gauge	rectangular 3.7×1.3
Material of the housing	Metal
Standard	ISO 13385

Measuring range	0 - 100 mm
Jaw length	30 mm
Reversible reading	mm / inch
Depth gauge available	yes
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
Power supply	Battery-powered
Measurement deviation E MPE	± 0.02 mm
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

Calibration Calipers / depth gauges maximum measuring range 200 mm	011030 200
Labelling laser-etched Type	018940
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	011050 200
Calibration Calipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	021010 200

Accessories

Screw for depth gauge holder	412230
Button cell / special battery Battery type LR44	081560 LR44