



## Vernier depth gauge, Measuring range: 150mm



### Order data

Order number	418300 150
GTIN	4045197203632
Item class	41Z

### Description

#### Version:

**Measuring beam and vernier satin chrome-plated. Vernier adjustable.** High-contrast scale.  
**Measuring and contact faces precision lapped.** Wider bridging widths achievable by using extension base(see No. 418744).

#### Optional extras:

Additional extension base No. 418744 (180 – 320 mm).

Calibration: A1

Packaging: Wallet

Graduation: 1/20 mm

Vernier length: 39 mm

Bridge length: 100 mm

Cross-section measuring beam: 11×4 mm

### Technical description

Vernier length	39 mm
Measuring range	0 - 150 mm
Graduation	1/20 mm
Bridge length	100 mm
Cross-section measuring beam	11×4 mm
Packaging	Wallet
Standard	DIN 862

Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Calibration	A1
Type of product	Depth gauge

## Services

Calibration Calipers / depth gauges maximum measuring range 200 mm	011030 200
Labelling laser-etched Type	018940
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	011050 200
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	021010 200
Calibration Calipers / depth gauges maximum measuring range 200 mm	021000 200

## Accessories

Single extension base Bridge length 180 mm	418744 180
Single extension base Bridge length 260 mm	418744 260
Single extension base Bridge length 320 mm	418744 320