HOLEX

Digital depth gauge, Measuring range: 50mm



Order data

Order number	418760 50
GTIN	4045197927682
Item class	42A

Description

Version:

Digital depth gauge with **absolute scale**, no zeroing required. Very high accuracy due to the glass scale. Electronics switch off automatically after approx. 5 minutes and switch on again as soon as the tool is moved.

Supplied with:

1 battery No. 081560 size CR2032. Packaging: sturdy box Calibration: A1 Reversible reading: 0.01 mm Reversible reading: 0.0005 in Error limit: 0.02 mm Needle hole probe length: 6 mm Needle hole probe Ø: 1.5 mm Bridge length: 50 mm

Technical description

Article no of the battery / rechargeable battery fitted	081560 CR2032
Calibration	A1
Reversible reading	0.01 mm
Reversible reading	0.0005 in
Needle hole probe length	6 mm

Needle hole probe Ø	1.5 mm
Error limit	0.02 mm
Bridge length	50 mm
Number of batteries contained	1
Power supply	Battery-powered
Standard	Works standard
Reversible reading	mm / inch
Measured value saving	Once-off setting of the zero position
Measurement technology	digital
all parts	hardened
Packaging	sturdy box
Type of product	Depth gauge

Services

DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	011050 200
Calibration Calipers / depth gauges maximum measuring range 200 mm	011030 200
Labelling laser-etched Type	018940
Calibration Calipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	021010 200

Accessories

Button cell / special battery Battery type CR2032

081560 CR2032