



Try square Accuracy class 2, Stock length: 75X50mm



Order data

Order number	452600 75X50
GTIN	4045197205766
Item class	42F

Description

Version:

All faces and edges ground. Inspection test faces ground.

Application:

For accurate general workshop work.

Accuracy:

DIN 875 / 2 – angle tolerance e.g. for size 100×70 = 0.030 mm.

Standard: DIN 875

Calibration: F1

Right angle tolerance: 0.028 mm

Shank cross-section: 15×5 mm

Technical description

Shank cross-section	15×5 mm
Right angle tolerance	0.028 mm
Stock length	75×50 mm
Calibration	F1

Standard	DIN 875
Accuracy	2
Type of product	Try squares

Services

Calibration Stock, try, and bevel edge squares maximum arm length 100 mm	015020 100
Labelling laser-etched Type	018940
DAkkS calibration Stock, try, and bevel edge squares maximum arm length 750 mm	015600 750
DAkkS calibration Stock, try, and bevel edge squares maximum arm length 750 mm	025010 750
Recalibration Stock, try, and bevel edge squares maximum arm length 100 mm	025000 100

Accessories

Wooden case for stock length 75X50 mm	451600 75X50
---------------------------------------	--------------