

Tape measure, Length: 2m



Order data

Order number	461900 2
GTIN	4045197949257
Item class	41H

Description

Version:

A particularly high-quality tape measure with a body made from glass-fibre-reinforced polyamide and automatic tape return.

For the perfect grip, the contact areas and stop button are coated with **2-component Haptoprene**.

Plain bearings with Teflon ensure smooth action and exceptionally easy running.

Innovative dampers of special rubber absorb the reaction energy and protect the wrist. **Aluminium profile inserted** on the underside for precise standing.

A special clear lacquer protects the tape against wear. The additional anti-glare correction ensures clear visibility under all light conditions.

mm graduation Calibration: G1 Standard: EG II Tape width: 13 mm Body length: 62 mm Body width: 26 mm Body height: 59 mm

Technical description

Body height	59 mm
Band length	2 m
Tape width	13 mm
Body length	62 mm
Body width	26 mm
Standard	EG II
Calibration	G1
Type of product	Measuring tape

Services

Calibration Locking tape measure maximum length 2 m	016140 2
Labelling laser-etched Type	018940
Calibration Tape measure maximum length 2 m	026240 2
DAkkS Calibration locking tape measure 5	026250 5