# Garant

#### Tape measure, Length: 5m



### Order data

Order number	461900 5
GTIN	4045197949271
Item class	41H

#### Description

#### Version:

A particularly high-quality tape measure with a body made from glass-fibre-reinforced polyamide and automatic tape return.

For the perfect grip, the contact areas and stop button are coated with **2-component Haptoprene**.

Plain bearings with Teflon ensure smooth action and exceptionally easy running.

**Innovative dampers** of special rubber absorb the reaction energy and protect the wrist.

Aluminium profile inserted on the underside for precise standing.

A special clear lacquer protects the tape against wear. The additional anti-glare correction ensures clear visibility under all light conditions.

mm graduation Calibration: G1 Standard: EG II Tape width: 16 mm Body length: 70 mm Body width: 30 mm Body height: 69 mm

#### **Technical description**

Tape width	16 mm
Body height	69 mm
Body length	70 mm
Body width	30 mm
Band length	5 m
Standard	EG II
Calibration	G1
Type of product	Measuring tape

## Services

Calibration Locking tape measure maximum length 5 m	016140 5
Labelling laser-etched Type	018940
DAkkS Calibration locking tape measure 5	026250 5
Calibration Tape measure maximum length 5 m	026240 5