

### Tape measure mm/inch, Length: 3m



#### **Order data**

Order number	4619103
GTIN	4045197949295
Item class	41H

## **Description**

#### **Version:**

A particularly high-quality tape measure with a body made from glass-fibre-reinforced polyamide and automatic tape return.

For the perfect grip, the contact areas and stop button are coated with **2-component Haptoprene**.

Plain bearings with Teflon ensure smooth action and exceptionally easy running.

**Innovative dampers** of special rubber absorb the reaction energy and protect the wrist. **Aluminium profile inserted** on the underside for precise standing.

A special clear lacquer protects the tape against wear. The additional anti-glare correction ensures clear visibility under all light conditions.

mm/inch graduations

Reversible reading: mm / inch

Standard: EG II Tape width: 13 mm Body length: 62 mm Body width: 26 mm Body height: 59 mm

## **Technical description**

Band length	3 m
Body length	62 mm
Body height	59 mm
Body width	26 mm
Tape width	13 mm
Standard	EG II
Calibration	G1
Reversible reading	mm / inch
Type of product	Measuring tape

# Services

Calibration Locking tape measure maximum length 5 m	016140 5
Labelling laser-etched Type	018940
Calibration Tape measure maximum length 5 m	026240 5
DAkkS Calibration locking tape measure 5	026250 5