

**Tape measure, Band length: 8m****Order data**

Order number	462010 8
GTIN	4045197879660
Item class	42G

Description**Version:**

Plastic casing with removable belt clip. Automatic tape return and stop, with damping effect. Sliding end hook. Tape measure printed black/red on yellow.

Calibration: G1

Standard: EG II

Tape width: 25 mm

Body length: 80 mm

Body width: 35 mm

Body height: 75 mm

Technical description

Body width	35 mm
Body height	75 mm
Band length	8 m
Tape width	25 mm
Body length	80 mm

Standard	EG II
Calibration	G1
Type of product	Measuring tape

Services

Calibration Locking tape measure maximum length 10/2 m	016140 10/2
Labelling laser-etched Type	018940
DAkkS Calibration locking tape measure 30/2	026250 30/2
Calibration Tape measure maximum length 10/2 m	026240 10/2