

Garant
Spirit level with selectable magnet, Length: 250 mm

Order data

Order number	467010 250
GTIN	4045197439116
Item class	41H

Description
Version:

Sturdy anodised aluminium profile. Flat and **Vee-form measuring faces**. The **selectable magnet** is effective on flat surfaces and **even on pipes**. Flush vials with magnifying effect create distortion-free views of the vial bubbles. The vertical head vial is also very clearly visible from above. **Error limit for overhead measurement: 0.5 mm/m.**

Callout:

Magnet switch

End face vial

can be read without problems from virtually any position.

Error limit in normal position: 0.5 mm/m

Technical description

Length	250 mm
Number of vertical vials	1
Through grip	no
Number of horizontal vials	1
Error limit in normal position	0.5 mm/m
Magnet	switchable
Type of product	Spirit level

Services

Labellinglaser-etched Type

018940