



Multimeter, Device type: 960



Order data

Order number	473320 960
GTIN	4045197838759
Item class	42I

Description

Version:

Ergonomically shaped two-component casing with rubber cover. Large easy-to-read digital display with switchable background lighting. Auto ranging meters. All meters with test prod mounting on the rear for one-hand operation, with a stand.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Application:

Digital service meters with comprehensive functions.

Standard:

IEC / DIN EN 61010-1; GS TÜV Rheinland und CE Zeichen.

Supplied with:

Supplied with batteries (2 pcs. size 960, 1 pc. size 9917), test prods No. 473328 size 2.

IP Index of Protection: IP 67

Information displayed: 4000

Display backlit: yes

Basic accuracy: 1 %

acoustic continuity test: yes

Diode testing: yes

Measurement process: TRUE RMS (AC)

Technical description

Frequency	0.01 Hz – 10 kHz
DC voltage	0.1 mV – 600 V
Display backlit	yes
Data storage key	yes
AC voltage	1 mV – 600 V
Overvoltage category	CAT III 600 V; CAT II 1000 V
Resistance	0.1 Ω – 40 M Ω
Measurement process	TRUE RMS (AC)
Basic accuracy	1 %
acoustic continuity test	yes
automatic power-off	yes
IP Index of Protection	IP 67
Diode testing	yes
Capacitance	0.01 nF – 4000 μ F
Information displayed	4000
Illumination of probe points	yes
AC current	0.1 μ A – 10 A
DC current	0.1 μ A – 10 A
Number of batteries contained	2
Article no of the battery / rechargeable battery fitted	081551 LR3
Power supply	Battery-powered
Power supply	2x No. 081556 size LR3
Type of product	Multimeter

Services

Labelling laser-etched Type	018940
-----------------------------	--------

Accessories

Test leads Measuring tips Ø 2 mm	473328 2
Alkaline-manganese batteries International size LR3	081556 LR3
Alkaline-manganese batteries International size LR3	081561 LR3