



Combination spanner, chrome-plated, Width across flats: 12mm



Order data

Order number	613950 12
GTIN	4045197159786
Item class	62A

Description

Version:

Drop-forged. With close tolerance jaw width.
With oval shaft.

Standard:

DIN 3113 A / ISO 3318 / ISO 7738

Material:

Chrome vanadium steel, chrome-plated.
Spanner length L: 160 mm
maximum jaw height h₁: 5.5 mm
maximum ring height h_{2 max}: 10 mm

Technical description

Spanner length L	160 mm
maximum jaw height h ₁	5.5 mm
Width across flats	12 mm
Width across flats	metric
maximum ring height h _{2 max}	10 mm
Standard	DIN 3113 A
Standard	ISO 3318
Standard	ISO 7738
Ring setting	15 °

Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	chrome plated
Product name attribute	chrome-plated
Type of product	Spanner