



Combination spanner, chrome-plated, Width across flats: 22mm



Order data

Order number	613950 22
GTIN	4045197159878
Item class	62A

Description

Version:

Drop-forged. With close tolerance jaw width.
With oval shaft.

Standard:

DIN 3113 A / ISO 3318 / ISO 7738

Material:

Chrome vanadium steel, chrome-plated.
Spanner length L: 260 mm
maximum jaw height h₁: 10 mm
maximum ring height h_{2 max}: 15 mm

Technical description

Width across flats	22 mm
maximum jaw height h ₁	10 mm
Spanner length L	260 mm
Width across flats	metric
maximum ring height h _{2 max}	15 mm
Standard	DIN 3113 A
Standard	ISO 3318
Standard	ISO 7738
Ring setting	15 °

Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	chrome plated
Product name attribute	chrome-plated
Type of product	Spanner