



## Combination spanner, chrome-plated, Width across flats: 8mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 613950 8      |
| GTIN         | 4045197159748 |
| Item class   | 62A           |

### Description

#### Version:

Drop-forged. With close tolerance jaw width.  
With oval shaft.

#### Standard:

**DIN 3113 A / ISO 3318 / ISO 7738**

#### Material:

Chrome vanadium steel, chrome-plated.

Spanner length L: 120 mm

maximum jaw height h<sub>1</sub>: 4.5 mm

maximum ring height h<sub>2max</sub>: 7 mm

### Technical description

|                                       |            |
|---------------------------------------|------------|
| Spanner length L                      | 120 mm     |
| Width across flats                    | 8 mm       |
| maximum jaw height h <sub>1</sub>     | 4.5 mm     |
| Width across flats                    | metric     |
| maximum ring height h <sub>2max</sub> | 7 mm       |
| Standard                              | DIN 3113 A |
| Standard                              | ISO 3318   |
| Standard                              | ISO 7738   |
| Ring setting                          | 15 °       |

|                        |                       |
|------------------------|-----------------------|
| Manufacturing process  | drop forged           |
| Material               | Chrome vanadium steel |
| Surface                | chrome plated         |
| Product name attribute | chrome-plated         |
| Type of product        | Spanner               |