



Combination spanner, imperial, chrome-plated, Width across flats: 11/16in



Order data

Order number	613970 11/16
GTIN	4045197550705
Item class	62A

Description

Version:

Drop-forged. With close tolerance jaw width.
With oval shaft.

Standard:

DIN 3113 A / ISO 3318 / ISO 7738

Material:

Chrome vanadium steel, chrome-plated.
Spanner length L: 211 mm
maximum jaw height h₁: 8 mm
maximum ring height h_{2max}: 13 mm

Technical description

maximum jaw height h ₁	8 mm
Width across flats	11/16 in
Spanner length L	211 mm
Width across flats	imperial
maximum ring height h _{2max}	13 mm
Ring setting	15 °
Surface	chrome plated
Product name attribute	chrome-plated
Type of product	Spanner

