



Combination spanner, imperial, chrome-plated, Width across flats: 1/2in



Order data

Order number	613970 1/2
GTIN	4045197550071
Item class	62A

Description

Version:

Drop-forged. With close tolerance jaw width.
With oval shaft.

Standard:

DIN 3113 A / ISO 3318 / ISO 7738

Material:

Chrome vanadium steel, chrome-plated.

Spanner length L: 171 mm

maximum jaw height h₁: 6.5 mm

maximum ring height h_{2max}: 11 mm

Technical description

Width across flats	1/2 in
maximum jaw height h ₁	6.5 mm
Spanner length L	171 mm
Width across flats	imperial
maximum ring height h _{2max}	11 mm
Ring setting	15 °
Surface	chrome plated
Product name attribute	chrome-plated
Type of product	Spanner

