



## Combination spanner, imperial, chrome-plated, Width across flats: 5/8in



### Order data

Order number	613970 5/8
GTIN	4045197550095
Item class	62A

### Description

#### Version:

Drop-forged. With close tolerance jaw width.  
With oval shaft.

#### Standard:

**DIN 3113 A / ISO 3318 / ISO 7738**

#### Material:

Chrome vanadium steel, chrome-plated.  
Spanner length L: 201 mm  
maximum jaw height h<sub>1</sub>: 8 mm  
maximum ring height h<sub>2max</sub>: 13 mm

### Technical description

maximum jaw height h <sub>1</sub>	8 mm
Width across flats	5/8 in
Spanner length L	201 mm
Width across flats	imperial
maximum ring height h <sub>2max</sub>	13 mm
Ring setting	15 °
Surface	chrome plated
Product name attribute	chrome-plated
Type of product	Spanner

