



Combination spanner, imperial, chrome-plated, Width across flats: 7/16in



Order data

Order number	613970 7/16
GTIN	4045197550064
Item class	62A

Description

Version:

Drop-forged. With close tolerance jaw width.
With oval shaft.

Standard:

DIN 3113 A / ISO 3318 / ISO 7738

Material:

Chrome vanadium steel, chrome-plated.

Spanner length L: 151 mm

maximum jaw height h₁: 5.5 mm

maximum ring height h_{2max}: 10 mm

Technical description

Width across flats	7/16 in
maximum jaw height h ₁	5.5 mm
Spanner length L	151 mm
Width across flats	imperial
maximum ring height h _{2max}	10 mm
Ring setting	15 °
Surface	chrome plated
Product name attribute	chrome-plated
Type of product	Spanner

