

**Garant**
**Open ended spanner / ratchet ring spanner reversible 15° offset, Width across flats: 15mm**

**Order data**

Order number	614820 15
GTIN	4045197218803
Item class	61B

**Description**
**Version:**

Drop forged. Ring end with especially smooth–running reversible ring ratchet. Extremely small working arc of 5°.

**Material:**

Chrome vanadium steel, matt chrome-plated.

Spanner length L: 200 mm

Jaw width b: 33.4 mm

Jaw height  $h_1$ : 6.9 mm

Ring thickness  $h_2$ : 10 mm

Ring  $\varnothing$  D: 28.9 mm

Ratchet torque rating: 200 N·m

**Technical description**

Width across flats	15 mm
Spanner length L	200 mm
Ring thickness $h_2$	10 mm
Jaw height $h_1$	6.9 mm
Ratchet torque rating	200 N·m
Ring $\varnothing$ D	28.9 mm
Jaw width b	33.4 mm
Width across flats	metric

Ring setting	15 °
No. of teeth	72
Working arc	5 °
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	matt chrome-plated
Type of product	Spanner