

Garant
Open ended spanner / ratchet ring spanner reversible 15° offset, Width across flats: 18mm

Order data

Order number	614820 18
GTIN	4045197218834
Item class	61B

Description
Version:

Drop forged. Ring end with especially smooth-running reversible ring ratchet. Extremely small working arc of 5°.

Material:

Chrome vanadium steel, matt chrome-plated.

Spanner length L: 239 mm

Jaw width b: 38.6 mm

Jaw height h_1 : 8.1 mm

Ring thickness h_2 : 11.2 mm

Ring \varnothing D: 33.4 mm

Ratchet torque rating: 300 N·m

Technical description

Ratchet torque rating	300 N·m
Jaw width b	38.6 mm
Width across flats	18 mm
Spanner length L	239 mm
Ring \varnothing D	33.4 mm
Ring thickness h_2	11.2 mm
Jaw height h_1	8.1 mm
Width across flats	metric

Ring setting	15 °
No. of teeth	72
Working arc	5 °
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	matt chrome-plated
Type of product	Spanner