

**Garant****Open ended spanner / ratchet ring spanner set, imperial, Width across flats: 1in****Order data**

Order number	614825 1
GTIN	4045197331298
Item class	61B

**Description****Version:**

Drop forged. Ring end with especially smooth-running reversible ring ratchet. Extremely small working arc of 5°.

**Material:**

Chrome vanadium steel, matt chrome-plated.

Spanner length L: 325 mm

Jaw width b: 50.8 mm

Jaw height  $h_1$ : 10.2 mm

Ring thickness  $h_2$ : 14.5 mm

Ring  $\varnothing$  D: 47.1 mm

Ratchet torque rating: 500 N·m

**Technical description**

Jaw height $h_1$	10.2 mm
Width across flats	1 in
Ratchet torque rating	500 N·m
Jaw width b	50.8 mm
Ring thickness $h_2$	14.5 mm
Spanner length L	325 mm
Ring $\varnothing$ D	47.1 mm
Width across flats	imperial

Ring setting	0 °
No. of teeth	72
Working arc	5 °
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	matt chrome-plated
Type of product	Spanner