

Garant
Open ended spanner / ratchet ring spanner set, imperial, Width across flats: 3/4in

Order data

Order number	614825 3/4
GTIN	4045197331281
Item class	61B

Description
Version:

Drop forged. Ring end with especially smooth–running reversible ring ratchet. Extremely small working arc of 5°.

Material:

Chrome vanadium steel, matt chrome-plated.

Spanner length L: 250 mm

Jaw width b: 40.3 mm

Jaw height h_1 : 8.5 mm

Ring thickness h_2 : 11.5 mm

Ring \varnothing D: 34.5 mm

Ratchet torque rating: 325 N·m

Technical description

Spanner length L	250 mm
Width across flats	3/4 in
Jaw height h_1	8.5 mm
Ring \varnothing D	34.5 mm
Ring thickness h_2	11.5 mm
Jaw width b	40.3 mm
Ratchet torque rating	325 N·m
Width across flats	imperial

Ring setting	0 °
No. of teeth	72
Working arc	5 °
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	matt chrome-plated
Type of product	Spanner