

**Garant**
**Open ended spanner / ratchet ring spanner set, imperial, Width across flats: 5/16in**

**Order data**

Order number	614825 5/16
GTIN	4045197331212
Item class	61B

**Description**
**Version:**

Drop forged. Ring end with especially smooth–running reversible ring ratchet. Extremely small working arc of 5°.

**Material:**

Chrome vanadium steel, matt chrome-plated.

Spanner length L: 136 mm

Jaw width b: 17.7 mm

Jaw height  $h_1$ : 4.6 mm

Ring thickness  $h_2$ : 7 mm

Ring  $\varnothing$  D: 17.3 mm

Ratchet torque rating: 30 N·m

**Technical description**

Jaw width b	17.7 mm
Ring thickness $h_2$	7 mm
Width across flats	5/16 in
Jaw height $h_1$	4.6 mm
Ratchet torque rating	30 N·m
Ring $\varnothing$ D	17.3 mm
Spanner length L	136 mm
Width across flats	imperial

Ring setting	0 °
No. of teeth	72
Working arc	5 °
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	matt chrome-plated
Type of product	Spanner