

Garant
Reversible ratchet, 1/4 inch with ejector, Type: 1/4

Order data

Order number	632025 1/4
GTIN	4062406353940
Item class	61A

Description
Version:

Material selection and special forging method guarantee optimal functioning and long life. With reversing lever for right-hand and left-hand threads.

Standard:

Außenvierkante nach **DIN 3120-A 6,3** mit federnder Kugel, Innenvierkante nach **DIN 3120. DIN 3122-D 6,3**

Material:

Chrome vanadium steel, chrome-plated.

Suitable for :

Manual use.

Square drive: 1/4 in

No. of teeth: 36

Technical description

Square drive	1/4 in
Standard	DIN 3122
Standard	DIN 3120
overall length	115 mm
No. of teeth	36
Working angle	10°
Material	Chrome alloy steel
Surface	chrome-plated

Type of product

Ratchet

Accessories

Spare part assortment 1/4 inch Type 1/4

632028 1/4