

Precision electronics pliers set 3 pieces, Number of pliers: 3



Order data

| Order number | 700157 3 |
|--------------|---------------|
| GTIN | 4045197976451 |
| Item class | 71A |

Description

Version:

Precision machined with slim shape. Cutter induction hardened (62–64 HRC), jaws with smooth gripping faces. Non-reflecting surface, matt shot-blasted with inlaid joint and countersunk screw. Double interchangeable spring for easy operation. **2-component** grips made of conductive plastic. **Suitable for ESDs.** Cutting edges precision ground.

Material:

CNC-machined special tool steel for extremely accurate tolerances.

Supplied with:

1 electronics side cutter No. 726250 (pointed head): Size 125

1 electronics side cutter No. 726210 (normal head): Size 125

1 electronics snipe-nose pliers No. 727170: Size 140

Stored in: ABS plastic box Cutting chamfer: fine bevel

Technical description

| Number of pliers | 3 |
|------------------------------|---------|
| electrostatic characteristic | EGB/ESD |



| Cutting chamfer | without bevel |
|-----------------|-----------------------|
| Cutting chamfer | fine bevel |
| Material | Special tool steel |
| Type of product | Multi-function pliers |

Accessories

| Modular box Type 3 | 630315 3 |
|--|------------|
| Electronics side cutter, standard head shape Overall length 125 mm | 726210 125 |
| Electronics side cutter, pointed head Overall length 125 mm | 726250 125 |
| Electronics snipe-nosed pliers Overall length 140 mm | 727170 140 |