

Garant
Vanadium steel combination pliers, chrome-plated VDE insulated, overall length: 200 mm

Order data

Order number	701710 200
GTIN	4045197501431
Item class	71B

Description
Version:

Chrome vanadium steel. Serrated jaws. Cutting edges additionally induction hardened (approx. 64 HRC); suitable even for piano wire. **Insulated to DIN EN 60900 / VDE 0682-201.**

Pliers chrome-plated, handles with ergonomically optimised multi-component coverings with non-slip **Haptoprene** surface.

Standard:
DIN ISO 5746

Cutting capacity hard wire up to \varnothing : 2.5 mm

Cutting capacity piano wire up to \varnothing : 2 mm

Technical description

overall length	200 mm
Cutting capacity piano wire up to \varnothing	2 mm
Cutting capacity hard wire up to \varnothing	2.5 mm
Standard	DIN EN 60900 / VDE 0682-201
Standard	DIN ISO 5746
Handle	ergonomically optimised multi-component coverings, non-slip Haptoprene surface
Material	Chrome vanadium steel

Surface	chrome-plated
non-sparking	no
Type of product	Multi-function pliers