



## Vanadium combination pliers VDE insulated, Overall length: 160mm



### Order data

Order number	701852 160
GTIN	4045197887474
Item class	72B

### Description

#### Version:

Chrome vanadium steel. Serrated jaws. Cutting edges additionally induction hardened (approx. 64 HRC); suitable even for piano wire. **Insulated to DIN EN 60900 / VDE 0682-201.**

Pliers bright finished, handles with multi-component covering.

#### Standard:

##### DIN ISO 5746

Cutting capacity hard wire up to  $\varnothing$ : 2 mm

Cutting capacity piano wire up to  $\varnothing$ : 1.5 mm

### Technical description

Cutting capacity piano wire up to $\varnothing$	1.5 mm
Cutting capacity hard wire up to $\varnothing$	2 mm
overall length	160 mm
Standard	DIN EN 60900 / VDE 0682-201
Standard	similar to DIN ISO 5746
Handle	Multi-component covering
Material	Chrome vanadium steel.
Surface	bright finish
non-sparking	no
Type of product	Multi-function pliers

