

Garant

Water pump pliers with stepped fine adjustment, black, overall length: 250mm

**Order data**

Order number	706001 250
GTIN	4062406238988
Item class	71B

Description**Version:**

Box joint designed to prevent fingers being trapped. **Push-button fine step adjustment.** Concave profile serrated jaws, self-clamping. Surface manganese phosphated, polished teeth. Ergonomically shaped handles with non-slip plastic coating.

Standard:

DIN ISO 8976

Material:

Chrome vanadium steel, drop forged.

Hexagon across flats: 46 mm

Jaw capacity for pipes: 2 in

Number of fine adjustment steps: 25

Technical description

Hexagon across flats	46 mm
overall length	250 mm
Number of fine adjustment steps	25
Jaw capacity for pipes	2 in
Surface	manganese phosphated, polished jaws
Standard	DIN ISO 8976
Type of jaws	concave profile serrated jaws

Material	Chromium vanadium steel
non-sparking	no
Quick adjustment	yes
Stepped fine adjustment	yes
Self-locking	yes
Protection against trapping fingers	yes
Type of product	Pipe wrench and water pump pliers