

**Universal grip wrench, jaw shape oval, overall length: 225 mm****Order data**

Order number	708005 225
GTIN	4045197717306
Item class	72B

**Description****Version:**

Serrated jaws and sturdy spring steel body. Span and clamping pressure adjustable with a knurled screw. Fully nickel-plated.

Jaw shape oval.

**Application:**

For clamping profiled and flat materials. Clamping force up to 10,000 N.

**Material:**

Jaws of chrome vanadium steel, drop forged.

Jaw length: 38 mm

Jaw capacity: 40 mm

**Technical description**

overall length	225 mm
Jaw capacity	40 mm
Jaw length	38 mm
Type of product	Grip wrench