

**Universal grip wrench, jaw shape oval, overall length: 300mm****Order data**

Order number	708005 300
GTIN	4045197719782
Item class	72B

**Description****Version:**

Serrated jaws and sturdy spring steel body. Span and clamping pressure adjustable with a knurled screw. Fully nickel-plated.

Jaw shape oval.

**Application:**

For clamping profiled and flat materials. Clamping force up to 10,000 N.

**Material:**

Jaws of chrome vanadium steel, drop forged.

**Spare part:**

Spare spring No. 708301 size 12.

Jaw length: 47 mm

Jaw capacity: 60 mm

**Technical description**

overall length	300 mm
Jaw capacity	60 mm
Jaw length	47 mm
Type of product	Grip wrench

**Accessories**

Spring Type 12

708301 12