Garant

Snipe nose pliers, angled VDE insulated, overall length: 200 mm



Order data

Order number	713710 200
GTIN	4045197501493
Item class	71B

Description

Version:

Very long snipe nose jaws. Cutting edges induction hardened (approx. 61 HRC), suitable for hard and soft wire. Serrated inside jaws. **Plastic-coated handles to DIN EN 60900 / VDE 0682-201** for working at voltages up to 1000 V

Jaws chrome-plated, handles with ergonomically optimised multi-component coverings with non-slip **Haptoprene** surface.

Standard:

DIN ISO 5745

Material:

Chrome vanadium steel, drop-forged and oil-hardened. Jaw length: 73 mm

Technical description

overall length	200 mm
Jaw length	73 mm
Jaw design	snipe-nosed with angled jaws (approx. 40° - 45°)
Standard	DIN EN 60900 / VDE 0682-201
Standard	DIN ISO 5745
Jaw characteristics	Cutting edges induction hardened (approx. 60 HRC)
Type of jaws	inner face roughened

© Hoffmann GmbH Qualitätswerkzeuge

Handle	Multi-component covering with non-slip Haptoprene surface
Material	Chrome vanadium steel, drop- forged and oil-hardened
Surface	chrome-plated
Type of product	Multi-function pliers