



## Snipe-nose pliers, angled VDE insulated, Overall length: 160 mm



### Order data

Order number	713751 160
GTIN	4045197888013
Item class	72B

### Description

#### Version:

Very long snipe nose jaws. Cutting edges induction hardened (approx. 61 HRC), suitable for cutting hard and soft wire. Serrated inside jaws. **Plastic-coated handles to DIN EN 60900 / VDE 0682-201 for working at voltages up to 1000 V.**

Jaws bright finished, handles with multi-component covering.

#### Standard:

**DIN ISO 5745**

#### Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Jaw length: 50 mm

### Technical description

overall length	160 mm
Jaw length	50 mm
Jaw design	snipe nose with angled jaws (approx. 40° - 45°)
Standard	DIN EN 60900 / VDE 0682-201
Standard	similar to DIN ISO 5745
Jaw characteristics	Cutting edges induction hardened (approx. 60 HRC)
Type of jaws	inner face roughened

Handle	Multi-component covering
Material	Chrome vanadium steel, drop-forged and oil-hardened
Surface	bright finish
Type of product	Multi-function pliers