

Garant
Diagonal side cutter, chrome-plated VDE insulated, overall length: 180 mm


Order data

Order number	723510 180
GTIN	4045197501615
Item class	71B

Description

Version:

Heavy-duty head, induction hardened cutting edges (approx. 64 HRC), laid-on joint with no play.

Plastic-coated handles to DIN EN 60900 / VDE 0682-201 for working at voltages up to 1000 V

Jaws chrome-plated, handles with ergonomically optimised multi-component covering, with non-slip **Haptoprene®** surface.

Standard:

DIN ISO 5749

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Cutting capacity soft wire up to Ø: 3.8 mm

Cutting capacity hard wire up to Ø: 2.7 mm

Cutting capacity piano wire up to Ø: 2.2 mm

Technical description

overall length	180 mm
Cutting capacity hard wire up to Ø	2.7 mm
Cutting capacity soft wire up to Ø	3.8 mm
Cutting capacity piano wire up to Ø	2.2 mm
Standard	DIN EN 60900 / VDE 0682-201
Standard	DIN ISO 5749

Handle	Multi-component covering with non-slip Haptoprene surface
Manufacturing process	Cutting edges induction hardened (approx. 64 HRC)
Material	Chromium vanadium steel
Surface	chrome-plated
Heavy-duty diagonal side cutter	no
with selectable return spring	no
Type of product	Cutting pliers