

Garant
Diagonal side cutter, chrome-plated VDE insulated, overall length: 140 mm


Order data

Order number	725310 140
GTIN	4045197501639
Item class	71B

Description

Version:

Slim shape with induction hardened cutting edges (approx. 62 HRC). **Plastic-coated handles to DIN EN 60900 / VDE 0682-201 for working at voltages up to 1000 V.**

Jaws chrome-plated, handles with ergonomically optimised multi-component covering, with non-slip **Haptoprene®** surface.

Standard:

DIN ISO 5749

Material:

Special tool steel, drop-forged, and oil-hardened.

Cutting capacity soft wire up to Ø: 4 mm

Cutting capacity hard wire up to Ø: 1.8 mm

Technical description

Cutting capacity hard wire up to Ø	1.8 mm
Cutting capacity soft wire up to Ø	4 mm
overall length	140 mm
Standard	DIN EN 60900 / VDE 0682-201
Standard	DIN ISO 5749
Handle	Multi-component covering
Manufacturing process	Cutting edges induction hardened (approx. 62 HRC)

Material	Special tool steel
Surface	chrome-plated
Heavy-duty diagonal side cutter	no
with selectable return spring	no
Type of product	Cutting pliers