



Diagonal side cutter VDE insulated, overall length: 160mm



Order data

Order number	725351 160
GTIN	4045197888075
Item class	72B

Description

Version:

Slim shape with induction hardened cutting edges (approx. 62 HRC). **Plastic-coated handles to DIN EN 60900 / VDE 0682-201 for working at voltages up to 1000 V.**

Jaws bright finished, handles with multi-component covering.

Standard:

DIN ISO 5749

Material:

Special tool steel, drop-forged and oil-hardened.

Cutting capacity soft wire up to Ø: 4 mm

Cutting capacity hard wire up to Ø: 2 mm

Technical description

overall length	160 mm
Cutting capacity soft wire up to Ø	4 mm
Cutting capacity hard wire up to Ø	2 mm
Standard	DIN ISO 5749
Standard	DIN EN 60900 / VDE 0682-201
Handle	Multi-component covering
Manufacturing process	Cutting edges induction hardened (approx. 62 HRC)

Material	Special tool steel
Surface	bright finish
Heavy-duty diagonal side cutter	no
with selectable return spring	no
Type of product	Cutting pliers