

**Garant**

**Electronics side cutter, pointed head, hollowed jaws, kW, Overall length: 125mm**


**Order data**

Order number	726255 125
GTIN	4045197976611
Item class	71B

**Description**
**Version:**

Precision machined with slim shape. Cutting edges induction hardened (62 - 64 HRC). Non-reflecting surface, matt shot-blasted with inlaid joint and countersunk screw. Double interchangeable springs for easy operation. **2-component** conductive grips. **Suitable for ESDs**. Cutting edges precision ground.

**Material:**

CNC-machined special tool steel for extremely accurate tolerances.

Cutting chamfer: without bevel

Head width: 10 mm

Cutter length: 10 mm

Cutting capacity copper wire up to  $\varnothing$ : 0.1 - 1 mm

**Technical description**

Cutting capacity copper wire up to $\varnothing$	0.1 - 1 mm
Cutter length	10 mm
Head width	10 mm
overall length	125 mm
electrostatic characteristic	EGB/ESD
Cutting chamfer	without bevel

Product name attribute	kW
Type of product	Cutting pliers