



Adjustable spanner with coated handle, overall length: 250 mm



Order data

Order number	813961 250
GTIN	4062406069704
Item class	82A

Description

Version:

Slim design with double-T-profile shank (chromium plated). Jaw angle 22°. Drop-forged and hardened. With **scale** on the jaw.

With non-slip grip.

Adjustable spanner, chrome-plated.

maximum width across flats: 30 mm

overall length: 10 inch

Technical description

maximum width across flats	30 mm
overall length	10 inch
overall length	250 mm
Jaw position	22 degrees
non-sparking	no
Scaling	yes
Grips	yes
Type of product	Spanner

