

Garant GRIDLINE

ToolCar roller cabinet, 20×16G, Number of drawers: 7



Order data

| | |
|--------------|---------------|
| Order number | 914520 7 |
| GTIN | 4045197892102 |
| Item class | 9GT |

Description

Version:

The ToolCar roller cabinet with scratch resistant, anti-slip and extremely surface-friendly **GARANT GridLine mat**. Easy exchange of the tray with other worktops (for example, bamboo) or with a bamboo worktop with vice. Valuable cupboard / side cupboard can be locked centrally together with drawers. Drawer fronts and cabinet stiles are clad with LDPE bumpers. In the event of collisions they reduce the damage to vulnerable surfaces and tools.

Fitted with:

Drawer front height: 75; 75; 75; 75; 125; 125; 200 mm

Supplied with:

Supplied with dividers:

each 75 mm drawer 1 slotted partition No. 951510 size 75,

each 125 mm drawer 1 slotted partition No. 951510 size 125.

Colour:

Two-tone **powder-coated**, silver combined with RAL 7016 anthracite.

Note:

For drawers of height 200 mm, more suitable components now include slotted dividers No. 951510 size 200, edge partitions No. 951560 size 200, and divider inserts No. 951741 – 951821 each in size 200.

See group 95 for further accessories and dividing material. Suitable dividing material:

Slotted edge partitions No. 951560 size 75; size 125 and size 200;

Slotted dividers No. 951510 size 75; size 125 and size 200;
 Divider inserts No. 951721 – 951821 size 75; No. 951731 – 951821 size 125 and No. 951741 – 951821 size 200.

Cylinder lock: modular lock barrel

Individual drawer release system: One-hand

Drawer usable area in G: 20×16

Height: 1000 mm

Width: 800 mm

Depth: 500 mm

Drawer usable width: 500 mm

Drawer usable depth: 400 mm

Drawer usable width in G: 20

Technical description

| | |
|--|------------------------|
| Drawer usable width | 500 mm |
| Weight | 87 kg |
| Height | 1000 mm |
| Width | 800 mm |
| Number of drawers | 7 |
| Depth | 500 mm |
| Drawer usable depth | 400 mm |
| Drawer usable width in G | 20 |
| Drawer usable depth in G | 16 |
| Series | ToolCar roller cabinet |
| Series | ToolCar |
| Individual drawer release system | One-hand |
| Drawer usable area in G | 20×16 |
| Drawer/pull-out shelf load capacity | 40 kg |
| Drawer runner extension (partial/full extension) | 100 % |
| Drawer runner extension | Anti-tilt lock |
| Hoffmann perforated panel grid interval | 9×9 mm |
| Drawer usable width × usable depth in G | 20×16G |
| Cylinder lock | modular lock barrel |

| | |
|-----------------|----------------|
| Type of product | Roller cabinet |
|-----------------|----------------|

Accessories

| | |
|--|-------------|
| Slotted dividers Depth 16G suitable for drawer front height 75 mm | 951510 75 |
| Slotted dividers Depth 16G suitable for drawer front height 125 mm | 951510 125 |
| Set of wheels for roller cabinets and mobile workbenches Type G | 915567 G |
| Lock plate for GridLine Type VA21 | 914227 VA21 |