Garant GRIDUNG

Roller cabinet with full extension drawers, 20×16G, Number of drawers: 8



Order data

Order number	914540 8
GTIN	4045197892218
Item class	9GT

Description

Version:

Roller cabinet with scratch-resistant non-slip X-ABS tray, does not damage surfaces. The tray can easily be swapped with other worktops (e.g. bamboo) or with a bamboo worktop with vice.

Fitted with:

Drawer front height: 75; 75; 75; 75; 75; 125; 125; 125 mm

Supplied with:

Supplied with dividers:

each 75 mm drawer 1 slotted partition No. 951510 size 75,

each 125 mm drawer 1 slotted partition No. 951510 size 125.

Colour:

Two-tone **powder-coated**, silver combined with RAL 7016 anthracite.

Note:

Optional valuables cupboard / side cupboard No. 914791 not integrated in the central locking of the roller cabinet, closed by a separate cylinder lock.

For drawers of height 200 mm, more suitable components now include slotted dividers No. 951510 size 200, edge partitions No. 951560 size 200, and divider inserts No. 951741 – 951821 each in size 200.

See group 95 for further accessories and dividing material. Suitable dividing material:

Slotted edge partitions No. 951560 size 75 and size 125;

Slotted dividers No. 951510 size 75 and size 125;

Divider inserts No. 951721 – 951821 size 75 and No. 951731 – 951821 size 125.

Cylinder lock: modular lock barrel

Individual drawer release system: One-hand

Drawer usable area in G: 20×16

Height: 1000 mm Width: 800 mm Depth: 500 mm

Drawer usable width: 500 mm Drawer usable depth: 400 mm Drawer usable width in G: 20

Technical description

Height	1000 mm
Drawer usable width	500 mm
Depth	500 mm
Number of drawers	8
Weight	78.2 kg
Drawer usable depth	400 mm
Width	800 mm
Drawer usable width in G	20
Drawer usable depth in G	16
Individual drawer release system	One-hand
Drawer usable area in G	20×16
Drawer/pull-out shelf load capacity	40 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Hoffmann perforated panel grid interval	9×9 mm
Drawer usable width \times usable depth in G	20×16G
Cylinder lock	modular lock barrel
Type of product	Roller cabinet



Accessories

Slotted dividers Depth 16G suitable for drawer front height 75 mm	951510 75
Slotted dividers Depth 16G suitable for drawer front height 125 mm	951510 125
Set of wheels for roller cabinets and mobile workbenches Type G	915567 G
Lock plate for GridLine Type VA21	914227 VA21