#### **Garant GRID**UNG

# Roller cabinet with drawers 75 kg, $26 \times 24G$ , Height mm / number of drawers: 985/7



## **Order data**

Order number	931145 985/7
GTIN	4062406352660
Item class	9GK

# **Description**

# **NOTE: Colour selection possible**

#### **Version:**

### Complete with drawers 26×24G.

Roller cabinet in 30×28G with 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, castors with parking brakes. With anti-roll lip on 4 sides, ribbed rubber mat and 2-component Haptoprene® push handles. An anti-tilt device prevents more than one drawer being opened at one time. The casing can be locked centrally with a cylinder lock.

100% full extension drawers with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

With **individual drawer release system** prevents the opening of drawers during transport. Absolutely necessary for all roller cabinets.

## **Colour:**

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated**. **Drawer body not configurable**, **always RAL 7035 light grey**.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Drawer/pull-out shelf load capacity: 75 kg

Drawer runner extension (partial/full extension): 100 %

Individual drawer release system: One-hand

Drawer usable area in G: 26×24

Height: 985 mm Width: 750 mm Depth: 700 mm

Usable height: 700 mm Drawer body height: 800 mm Drawer body usable height: 700 mm

# **Technical description**

Drawer body usable height	700 mm
Drawer usable depth in G	24
Drawer usable width in G	26
Number of doors	0
Depth	700 mm
Drawer/pull-out shelf load capacity	75 kg
Width	750 mm
Drawer body height	800 mm
Individual drawer release system	One-hand
maximum load capacity	600 kg
Drawer usable depth	600 mm
Number of fixed wheels without parking brake	2
Usable height	700 mm
with anti-roll lip	yes
Electronic locking system can be retrofitted	yes
Drawer usable area in G	26×24
ComfortClose	no
Number of drawers	7
Treadless tyres	yes
Height	985 mm
Drawer usable width	650 mm
Number of castors with parking brake	2
Wheel ∅	125 mm

Drawer runner extension (partial/full extension)	100 %
Weight	144 kg
Version	wheeled
Version	with drawers
Casing open at the top	no
Usable height for drawers	700 mm
Number of pull-out shelves	0
Material thickness	1.2 mm
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	26×24G

# Accessories

Roller cabinet for drawers Height mm / number of drawers 985/0	931147 985/0
Drawer with one-handed individual drawer release system, 75 kg Drawer front height 100 mm	931166 100
Drawer with one-handed individual drawer release system, 75 kg Drawer front height 150 mm	931166 150
Drawer with one-handed individual drawer release system, 75 kg Drawer front height 75 mm	931166 75
Sheet metal cover top with anti-roll lip on 4 sides Dimension in G 30X28	951972 30X28