



Swing door cabinet with viewing window swing doors, Height: 2000mm



Order data

Order number	949503 2000
GTIN	4062406080587
Item class	92S

Description

NOTE: Colour selection possible

Version:

Body and doors made of 0.9 mm sheet metal, storage shelf mountings at 40 mm intervals.

Doors reinforced on the inside and can be locked by push handle with a **cylinder lock**. For more information on locking see No. 950050 – 950060.

With viewing window swing doors (polycarbonate windows).

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Colour selection: RAL 7035, RAL 7016, RAL 5005

Height: 2000 mm

Width: 1000 mm

Depth: 400 mm

Usable height: 1840 mm

Number of shelves: 4

Technical description

Cabinet fronts	Viewing window swing door
Height	2000 mm
Width	1000 mm
Usable height	1840 mm
Number of shelves	4
Handle positioning	centre
Depth	400 mm
Material thickness	0.9 mm
Shelf load capacity / maximum distributed shelf load (on metal)	60 kg
Cabinet housing internal load capacity	500 kg
Door opening angle	225 °
Height adjustment interval	40 mm
Cylinder lock	modular barrel
Colour selection	RAL 7035, RAL 7016, RAL 5005
Type of product	Filing cabinet

Accessories

Additional storage shelf Type 1000	949514 1000
------------------------------------	-------------