



Swing door cabinet with storage shelves, Height mm / Model: 1950/A



Order data

Order number	949531 1950/A
GTIN	4062406080594
Item class	92S

Description

NOTE: Colour selection possible

Version:

Body and doors of 0.9 mm sheet metal, storage shelf mountings at 40 mm intervals. Doors reinforced on the inside, can be locked by push handle with a **cylinder lock**. Complete with **4 shelves** of galvanised sheet metal.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Colour selection: RAL 7035, RAL 7016, RAL 5005

Height: 1950 mm

Width: 950 mm

Depth: 430 mm

Usable height: 1820 mm

Number of shelves: 4

Weight: 74 kg

Technical description

Weight	74 kg
Width	950 mm
Number of shelves	4
Usable height	1820 mm
Handle positioning	centre
Depth	430 mm
Height	1950 mm
Cabinet fronts	Plain sheet metal swing door
Model	A
Material thickness	0.9 mm
Shelf load capacity / maximum distributed shelf load (on metal)	80 kg
Cabinet housing internal load capacity	500 kg
Door opening angle	250 °
Height adjustment interval	40 mm
Cylinder lock	modular barrel
Colour selection	RAL 7035, RAL 7016, RAL 5005
Type of product	Filing cabinet

Accessories

Additional storage shelf Type 950	949534 950
-----------------------------------	------------