

Garant**Open storage bin, anthracite, Type: BC3****Order data**

| | |
|--------------|---------------|
| Order number | 963301 BC3 |
| GTIN | 4045197681973 |
| Item class | 91F |

Description**Version:**

Open storage bin with ergonomic handle (comfortable to carry). Can be converted to a storage box by fitting a transparent cover. Inner faces polished smooth, allowing easy removal of parts and easy cleaning. Facility to apply labels on labelling strips at the front, and also by inserting cards (credit card size 85.6 × 54 mm) at the back. Open storage bins are stackable.

Advantage:**GARANT open storage bins and their advantages:**

- **Sturdy and stable thanks to impact resistant polypropylene.**
- **High load capacity due to reinforced bases and side walls.**
- **Easily stacked using the registration points.**
- **Pleasant to handle and easy to clean due to high-quality surfaces and smooth inner faces.**
- **Wide variety of application options.**

Suitable for :

Storage bin racks No. 916535, 920240, for rack panels No. 957060 size S in modular cabinets and for shelving cabinets / wall cabinets No. 954600 - 954670 and No. 954701 to 954722. In addition, the bin support No. 963050 allows small open storage bins No. 963301 size AA1 and AB1 to be hung individually on perforated panels.

Note:

Easyfix Universal box holders No. 955810 size 100 are required for attaching to perforated panels.

Height: 165 mm

Width: 264 mm

Depth: 498 mm

Colour: anthracite

Technical description

| | |
|--|------------------------------|
| Type | BC3 |
| prepared for cover | yes |
| Height | 165 mm |
| prepared for EAN code on the rear | yes |
| Stop in drawers | no |
| Width | 264 mm |
| Depth | 498 mm |
| prepared for viewing window as loose goods divider | yes |
| stackable | yes |
| Facility to apply labels | by means of labelling strips |
| prepared for viewing window | yes |
| Colour | anthracite |
| Material | Polypropylene |
| Product name attribute | anthracite |
| Colour | anthracite |
| Type of product | Open storage bins |