

Garant**Swing away mounting and height adjuster with vice, Vice jaw width: 120 mm****Order data**

Order number	967565 120
GTIN	4045197806659
Item class	91J

Description**Version:**

Sturdy and very strong forged parts / steel design. Very smooth-running and precise guidance due to CNC-machined components. Extremely strong clamping by the special locking device. Quicker clamping in any desired position by means of the safety clamping lever.

Safety function: The vice can be swung down to the correct lower position only when the fixing pin is engaged in the notch on the lift tube.

Advantage:

- **The vice, in conjunction with the height adjuster can be rotated through 360°, without the use of an additional swivel base.**
- **The vice can be swung away under the bench to provide a clear working area.**
- **Installation in a lockable cupboard with a door allows the swing away mounting and height adjuster to be stowed away and protected against theft (casing available on request).**

Application:

For matching the height of the vice to the ergonomically ideal working height, to the nearest centimetre.

Supplied with:

Fasteners for attachment under the worktop. Vice No. 967100 size 120.

Colour:

Silver-grey

Height adjustment range: 132 mm
Height retracted: 296 mm
Weight: 27 kg

Technical description

Height retracted	296 mm
Weight	27 kg
Height adjustment range	132 mm
Type of product	Height adjuster