

Gravity: 4-Digital LED Segment Display Module (Red)

SKU:DFR0645-R

FEATURES

- Display Mode: 8 segment×4 digit
- Support 8-level brightness adjustment
- IIC communication


SPECIFICATION

- Operating Voltage: DC 5V
- Operating Current: <55mA
- Operating Temperature: -40 °C ~ +85 °C
- Storage Temperature: -55 °C ~ +125 °C
- Digital Tube Size: 5.05× 1.9cm/2.0×0.75"
- PCB Size: 6.7×2.2 cm/2.64×0.87"


SHIPPING LIST

- 4-Digital LED Segment Display Module (Red) x1
- Gravity-4Pin IIC Connector x1

INTRODUCTION








01 Adjustable Brightness

Two colors to choose from (Red/Green), 8-level brightness adjustment



Standard IIC port, compatible with Gravity interface, easy to use







Delicate appearance, steady performance and small size (67×22mm)