
## 1. Part No. Expression:

## <u>SCR35018R3KB</u>

(a) (b) (c) (d)(e)

- a) Series code d) Tolerance Code
- b) Dimension code e) Internal Code
- c) Inductance Code

## 2. Configuration & Dimensions: (Unit-mm)



A	В	С	D
35.0 ±0.5	1.2 Max	37.0 ± 3.0	5.0 Ref

Note: Dimension B does not include release paper.

NOTE: Specifications subject to change without notice. Please check our website for latest information.

3. Schematic:




# 4. Electrical Characteristics:

Inductance (uH)	Test Frequency (Hz)	DCR (mΩ)	Irms (mA)
8.3±10%	1V/100K	160 Max	2000 Max

## 5. General Specifications:

- a) Operating Temp.: -40°C ~ +85°C
- b) Storage Temp.: -40°C ~ +85°C (packaging)
- c) Irms: Based on temp. rise up to 40°C Max.
- d) Power Rating: 5W

#### 6. Material List:



- (a) Mn-Zn Ferrite Sheet (Thickness: 0.5mm Typ)
- (b) Adhesive
- (c) Wire

SUPERWORLD ELECTRONICS (S) PTE LTD

NOTE: Specifications subject to change without notice. Please check our website for latest information.