

ACS725 Stromsensor Breakout +-30A (AC)

Item number: 201876-002

This is a breakout with the ACS724 current sensor from Allegro MicroSystems.
Supply voltage: 3,3V

Category: **Current**

- band with: 120 kHz
- typical error of less than 1.5%.
- internal resistance is typically 1.2 mOhm
- supply voltage: 3,3V

20A (AC) Version

- resolution: 66mV/A
- Sensor: ACS725LLCTR-20AB-T

30A (AC) Version

- resolution: 44mV/A
- Sensor: ACS725LLCTR-30AB-T

10A (DC) Version

- resolution: 264mV/A
- Sensor: ACS725LLCTR-10AU-T